

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

SE series

Size	3S
Series	S - Indoor Stepped Insert

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/brf-3s-200-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility	No
------------------------------------	----


Form & Material

Shell style / Model id	BRF - Cap for free receptacle
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet and crimping tube, brass (chrome plated [SAE AMS 2460]) collet nut
Keying	No keying
Colour	Grey
Weight	21.52 g

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP61
Temperature range	-55°C / +135°C
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr

Drawings



No keying

Dimensions

	A	B	L	M	N
mm.	22	14	18	8	120
in.	0.87	0.55	0.71	0.31	4.72

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/brf-3s-200-nas.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.