

[Standard](#)

Image for illustrative purpose only

Summary

[Request a quote](#)[P series catalog](#)[Industry Brochure Medical](#)

Number of contacts Low Voltage	10
Nb of contacts Fluidic	1
Wire Size/AWG	30 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.30 - 9.20 mm
Size	2P
Suggested matching part	CKB.015.GLLG
Series	REDEL P - Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cab-015-gla-c92gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Solder
Nb of contacts Fluidic	1
Insert configuration value	2P.015 - 1 Fluidic, 10 Low V.
Insulator	L: PEEK for solder contacts
Rated current	5 A
Test voltage contact-contact	1.63 (kV DC)
Air clearance	0.9 mm
Creepage distance	0.9 mm
Contact Dia.	0.7 mm (0.028 in)
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	CA - Straight plug with cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	PSU (Polysulfone), grey
Locking system	Push-pull
Keying	B: 3 keys (alpha=0, gamma=60, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	9.34 g

Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
Temperature range	-50°C / +150°C


https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cab-015-gla-c92gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.30 - 9.20 mm

Drawings



Recommended By Lemo

Bend Reliefs		
GMA.2B.080.RG	GMA.2B.080.RA	GMA.2B.080.RB
GMA.2B.080.RJ	GMA.2B.080.RM	GMA.2B.080.RN
GMA.2B.080.RR	GMA.2B.080.RS	GMA.2B.080.RV

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cab-015-gla-c92gz.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.