

[Standard](#)

Image for illustrative purpose only

Summary

[Request a quote](#)[P series catalog](#)[Industry Brochure Medical](#)[Customer Drawing](#)

Number of contacts Low Voltage	34
Gender	Reverse Gender
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 7.20 mm
Size	2P
Suggested matching part	CLH.M34.SLAG
Series	REDEL P - Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cah-m34-sll-c72gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	34
Contact Termination Low voltage	Solder
Insert configuration value	2P.M34 - 34 Low V.
Insulator	L: PEEK for solder contacts
Rated current	1.5 A
Test voltage contact-contact	0.92 (kV DC)
Air clearance	0.3 mm
Creepage distance	0.3 mm
Gender	Reverse Gender

Form & Material

Shell style / Model id	CA - Straight plug with cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	PEI (Polyetherimide), grey
Locking system	Push-pull
Keying	H: 3 keys (alpha=0, gamma=80, Plug: female contacts, Receptacle: male contacts)
Colour	Grey
Weight	11.35 g

Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
Temperature range	-50°C / +170°C
F ret (max)	250 N
F ret (min)	150 N
Steam sterilization	Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us.

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cah-m34-sll-c72gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 7.20 mm

Recommended By Lemo

Bend Reliefs

GMA.2B.063.RG	GMA.2B.063.RA	GMA.2B.063.RB
GMA.2B.063.RJ	GMA.2B.063.RM	GMA.2B.063.RN
GMA.2B.063.RR	GMA.2B.063.RS	GMA.2B.063.RV

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/cah-m34-sll-c72gz.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.