



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Technical details

Form & Material

Shell style / Model id	DCD - Torque wrench for collet nut
Keying	No keying
Weight	144.2 g

Environment

Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

Drawings



No keying

Dimensions

S1

mm.	9
in.	0.35

https://www.lemo.com/int_en/catalog/product/view/id/417225/s/dcd-1b-015-pa090/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.