

Standard




Image for illustrative purpose only

Summary

[Request a quote](#)

[unipole multipole](#)

https://www.lemo.com/int_en/dcg-91-201-4tn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Shell style / Model id	DCG - Spanners for hexagonal nuts
Keying	No keying
Weight	83.71 g

Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Drawings

No keying

Dimensions

	B	L	N
mm.	20	52	65
in.	0.79	2.05	2.56

https://www.lemo.com/int_en/dcg-91-201-4tn.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.