



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

---

BKT series

# Technical details

## Form & Material

Keying	No keying
Weight	52.88 g

## Environment

Environmental sealing (IP rating)	No IP rating
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

## Drawings

No keying

[https://www.lemo.com/int\\_en/dcs-3k-175-72ln.html](https://www.lemo.com/int_en/dcs-3k-175-72ln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.