

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

SE series

[Customer Drawing](#)

Number of contacts Low Voltage	4
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	0S
Suggested matching part	FFA.0S.304.CLAC17
Series	S - Indoor Stepped Insert

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-304-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	0S.304 - 4 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	A (General Design Producibility - Preferred)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 A
Test voltage (kV DC)	1.5
Contact Dia.	0.7 mm (0.028in)

Form & Material

Shell style / Model id	ECP - Fixed receptacle with two nuts, long threaded shell, with straight contact for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Colour	Grey
Weight	4.94 g

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-304-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Panel Drill Hole	M9
------------------	----

Recommended By Lemo

Accessories

Compatible cap	BRE.0S.200.NAS
----------------	--------------------------------

Tools

Spanner 2	DCM.65.106.AZ4
-----------	--------------------------------

Spanner wrench	Socket for torque wrench DCM.0S.M09.4
----------------	---

CAD

Documents

PCB	Download
-----	--------------------------

PCB Eagle	Download
-----------	--------------------------

Kicad	Download
-------	--------------------------

PCB Altium	Download
------------	--------------------------

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ecp-0s-304-cln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.