

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

**BKT series**

Number of contacts Low Voltage	24
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Panel Drill Hole	M24
Size	3K
Suggested matching part	<a href="#">FGG.3K.324.CLAC95</a>
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	24
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	3K.324 - 24 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	A (General Design Producibility - Preferred)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 A
Vtest (contact-contact)	1.4 kV (DC)
Vtest (contact-shell)	1.1 kV (DC)
Contact Dia.	0.7 mm (0.028in)
Gender	Standard

## Form & Material

Shell style / Model id	EE - Fixed receptacle, nut fixing, with straight contacts for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	61.68 g
Panel Drill Hole	M24



[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>M</b>	<b>S1</b>	<b>P</b>	<b>N</b>
mm.	30	31	M24x1.0	7.5	4.5	22.5	12	31.3
in.	1.18	1.22		0.3	0.18	0.89	0.47	1.23

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

Compatible cap	<a href="#">BRE.3K.200.NAS</a>
----------------	--------------------------------

## Tools

---

Spanner 2	<a href="#">DCM.65.270.AZ</a>
-----------	-------------------------------

Spanner wrench	<a href="#">DCM.65.270.AZ</a>
----------------	-------------------------------

## CAD

### Documents

---

PCB	<a href="#">Download</a>
-----	--------------------------

PCB Eagle	<a href="#">Download</a>
-----------	--------------------------

Kicad	<a href="#">Download</a>
-------	--------------------------

PCB Altium	<a href="#">Download</a>
------------	--------------------------

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-324-cln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.