

Standard*Image for illustrative purpose only*

Summary

[Request a quote](#)**BKT series**

Number of contacts Low Voltage	10
Number of contacts High Voltage	2
Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.00 - 22.60 mm
Size	3K
Suggested matching part	FGG.3K.740.CJAC85Z
Series	K - Outdoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Solder
Number of contacts High Voltage	2
Contact Termination High voltage	Solder
Insert configuration value	3K.740 - 2 High V. 10 Low V.
Footprint IPC Class3 compatibility	No
Insulator	J: PEEK/PEEK
Rated current	2 A
Rear of connector must be protected	ATUM
Test voltage HV Ue (kV rms)	17.1
Working voltage LV Ue (kV rms)	0.2
Air clearance	12.7 mm
Contact Dia.	0.7
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	EE - Fixed receptacle, nut fixing (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	59.38 g

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-740-cjl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Jacket cable outside diameter [mm]	2.00 - 22.60 mm
Panel Drill Hole	M24

Drawings



Dimensions

	A	B	e	E	L	M	N	P	S1
mm.	30	31	M24x1.0	7.5	36.2	4.5	33.6	12	22.5
in.	1.18	1.22		0.3	1.43	0.18	1.32	0.47	0.89

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-740-cjl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories

Compatible cap	BRE.3K.200.NAS
----------------	----------------

Tools

Spanner 2	DCM.65.270.AZ
-----------	---------------

Spanner wrench	DCM.65.270.AZ
----------------	---------------

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/eeg-3k-740-cjl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.