

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

Coax triax mixed en

Number of contacts Low Voltage	2
Nb of contacts Coax	3
Wire Size/AWG	24 - 20
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Panel Drill Hole	M24
Jacket cable outside diameter [mm]	2.00 - 22.60 mm
Size	3K
Suggested matching part	<a href="#">FGG.3K.862.CLCC101</a>
Series	K - Outdoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	2
Contact Termination Low voltage	Crimp
Nb of contacts Coax	3
Contact Termination Coax - Conductor fixing	Crimp
Contact Termination Coax - Screen fixing	Crimp
R (max)	5.8 mOhm
Insert configuration value	3K.862 - 3 Coax (50 Ohm), 2 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	9 A
Impedance	50 Ohms
Test voltage (kV DC)	1.6
Max. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Min. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Cable type	RG 178 B/U, RG 196 A/U
Contact Dia.	0.7 mm (0.03in)
Wire Size/AWG	24 - 20
Gender	Standard

## Form & Material

Shell style / Model id	EG - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	69.66 g
Panel Drill Hole	M24

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Jacket cable outside diameter [mm]	2.00 - 22.60 mm
------------------------------------	-----------------

## Drawings



## Dimensions

	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>N</b>	<b>S1</b>	<b>S3</b>	<b>A</b>	<b>B</b>
mm.	M24x1.0	11	36.2	6	33.6	22.5	30	31	34.5
in.		0.43	1.43	0.24	1.32	0.89	1.18	1.22	1.36

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

Replacement contact EGG.3B.660.ZZM

Compatible cap BRE.3K.200.NAS

## Tools

---

Die Tool DPE.99.103.1K

Positionner DCE.91.093.BVM

Extraction tool DCC.09.05B.LAG

Crimp tool DPC.91.701.V

[https://www.lemo.com/int\\_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html](https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/egg-3k-862-clm2.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.