

Standard




Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Number of contacts Low Voltage	7
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Elbow
Locking system	Push-pull
Size	0B
Suggested matching part	FGG.0B.307.CLAD56
Series	B - Indoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	7
Contact Termination Low voltage	PCB - Straight
R (max)	8.7 mOhm
Insert configuration value	0B.307/EPG - 7 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	A (General Design Producibility - Preferred)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2 A
Test voltage contact-contact	1.1 kV DC
Test voltage contact-shell	1 kV DC
Contact Dia.	0.5 mm (0.02in)
Gender	Standard

Form & Material

Shell style / Model id	EP.HLN - Elbow receptacle for printed circuit (solder or screw fixing)
Socket / Receptacle	Elbow
Housing material	PPS (Polyphenylene) shell, other pieces nickel plated [SAE AMS QQ N 290] brass
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	9.79 g

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/epg-0b-307-hln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr

Recommended By Lemo

Caps

Compatible cap	BRE.OS.200.NAS
Cap 2	BRE.OS.200.NPSN
Plastic Cap	BRA.OB.200.PCSG
Soft Cap	BEZ.OB.200.SCN

CAD

Documents

PCB Eagle	Download
-----------	--------------------------

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/epg-0b-307-hln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.