

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

| | |
|--------------------------------|-----------------------------------|
| Number of contacts Low Voltage | 18 |
| Wire Size/AWG | 24 - 20 |
| Gender | Standard |
| Plug | Plug - Fixed |
| Locking system | Snap-on |
| Size | 3B |
| Suggested matching part | PHG.3B.318.CLLD12 |
| Series | B - Indoor keyed |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-318-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage | 18 |
| Contact Termination Low voltage | Crimp |
| R (max) | 4.8 mOhm |
| Insert configuration value | 3B.318 - 18 Low Voltage |
| Insulator | Y: PEEK for crimp contacts |
| Rated current | 7 A |
| Vtest (contact-contact) | 2.6 kV (DC) |
| Vtest (contact-shell) | 2.3 kV (DC) |
| Contact retention | 30 N |
| Max. Conductor | 0.5 mm ² (AWG 20) |
| Min. Conductor | 0.25 mm ² (AWG 24) |
| Bucket Dia. | 1.1 mm (0.043in) |
| Contact Dia. | 0.9 mm (0.035in) |
| Wire Size/AWG | 24 - 20 |
| Gender | Standard |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | FA - Fixed plug, non-latching, nut fixing |
| Plug | Fixed |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Snap-on |
| Keying | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Colour | Grey |
| Weight | 38.22 g |


https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-318-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

| | |
|-----------------------------------|--|
| Technical domain | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +250°C (max. temperature valid for short periods of use.) |
| Climatic Category | 55/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >1000 hr |

Drawings



Dimensions

| | A | B | e | E | L | M | N | S1 | S3 |
|-----|----------|----------|----------|----------|----------|----------|----------|-----------|-----------|
| mm. | 22 | 25.2 | M18x1.0 | 5.8 | 32.1 | 17 | 30.2 | 16.5 | 22 |
| in. | 0.87 | 0.99 | | 0.23 | 1.26 | 0.67 | 1.19 | 0.65 | 0.87 |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-318-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo



Accessories

| | |
|---------------------|----------------|
| Replacement contact | FGG.3B.560.ZZC |
|---------------------|----------------|

Tools

| | |
|-----------------|----------------|
| Spanner | DCA.91.282.2TN |
| Extraction tool | DCC.09.05B.LAG |
| Crimp tool | DPC.91.701.V |

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|---------------|--------|---|
| CMN.18.T30.048QGZE | TPR (medical) | Grey |  |
| 218220 | PVC | Black |  |
| 218240 | PVC | Black |  |
| 218260 | PVC | Black |  |
| 236080 | PVC | Grey | |
| 318250 | PVC | Grey |  |

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fag-3b-318-cyc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.