



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

---

[unipole multipole](#)

---

[Customer Drawing](#)

Jacket cable outside diameter [mm]	1.80 - 2.20 mm
------------------------------------	----------------

[https://www.lemo.com/int\\_en/ffa-00-722-cn.html](https://www.lemo.com/int_en/ffa-00-722-cn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	FFA - 00 series cable collet
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet
Keying	No keying
Weight	0.31 g

## Environment

Environmental sealing (IP rating)	IP50
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Salt Spray Corrosion	>1000 hr

## Cable fixation

Fixation type	Cable collet
Jacket cable outside diameter [mm]	1.80 - 2.20 mm

[https://www.lemo.com/int\\_en/ffa-00-722-cn.html](https://www.lemo.com/int_en/ffa-00-722-cn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.