

Special*Image for illustrative purpose only*

Summary

[Request a quote](#)

SE series

Customer Drawing

Jacket cable outside diameter [mm]	4.30 - 5.20 mm
Size	1S
Series	S - Indoor Stepped Insert

Technical details

Form & Material

Shell style / Model id	FFA - S series cable collet
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet
Keying	No keying
Weight	1.53 g

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Salt Spray Corrosion	>1000 hr

Cable fixation

Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.30 - 5.20 mm

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-1s-752-cn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.