

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

SE series

Number of contacts Low Voltage	7
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.10 - 5.50 mm
Size	2E
Suggested matching part	ERA.2E.307.CLL
Series	E - Outdoor Stepped Insert

Technical details

Electrical Configuration

Number of contacts Low Voltage	7
Contact Termination Low voltage	Solder
Insert configuration value	2E.307 - 3 (1.3 mm) + 4 (0.9 mm) Low Voltage
Footprint IPC Class3 compatibility	No
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	1.3 mm : 12 A, 0.9 mm : 9 A
Test voltage (kV DC)	1.2
Bucket Dia.	3x1.0 mm, 4x0.8 mm
Contact Dia.	3x1.3 mm, 4x0.9 mm
Wire Size/AWG details	1.3 mm : 20 (AWG max), 0.9 mm : 22 (AWG max)

Form & Material

Shell style / Model id	FFA - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Variant	Nut for fitting a bend relief

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-2e-307-clac55z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.10 - 5.50 mm

Drawings



Dimensions

	A	L	M	S2
mm.	16	52	36	12
in.	0.63	2.05	1.42	0.47

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-2e-307-clac55z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories

Compatible cap	BFA.2E.100.NAS
----------------	--------------------------------