

Standard

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[Catalog](#)[Customer Drawing](#)

Nb of contacts Triax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	8.10 - 8.50 mm
Size	2E
Suggested matching part	<a href="#">ERA.2E.675.CLL</a> <a href="#">PCA.2E.675.CTLC85Z</a>
Series	E - Outdoor Stepped Insert

# Technical details

## Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	2E.675 - 1 Triax (75 Ohm)
Insulator	T: PTFE
Rated current	6 A
Impedance	75 Ohms
VSWR	1.02 + 0.07 * f/GHz
Vtest	1200 V (AC), 1690 V (DC)
Cable type	Belden 8215,8232A, HF-2426, Triax 8 Nokia, 375 029 LEDE, RGT 179
Contact Dia.	0.9 mm (0.035in)

## Form & Material

Shell style / Model id	FFA - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	42.11 g

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-2e-675-ctac85z.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-2e-675-ctac85z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

---

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

---

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.10 - 8.50 mm

## Recommended By Lemo

### Accessories

---

Compatible cap	<a href="#">BFA.2E.100.NAS</a>
----------------	--------------------------------

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/ffa-2e-675-ctac85z.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/ffa-2e-675-ctac85z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.