

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

| | |
|------------------------------------|---|
| Number of contacts Low Voltage | 2 |
| Wire Size/AWG | 24 - 16 |
| Plug | Plug - Straight |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 5.30 - 6.20 mm |
| Size | 2S |
| Suggested matching part | ERA.2S.302.CLL PCA.2S.302.CLLC62 |
| Series | S - Indoor Stepped Insert |

Technical details

Electrical Configuration

| | |
|---------------------------------|----------------------------|
| Number of contacts Low Voltage | 2 |
| Contact Termination Low voltage | Solder |
| R (max) | 3.5 mOhm |
| Insert configuration value | 2S.302 - 2 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 20 A |
| Test voltage (kV DC) | 2.4 |
| Max. Solid Conductor | 1 mm ² (AWG 16) |
| Max. Stranded Conductor | 1 mm ² (AWG 18) |
| Bucket Dia. | 1.4 mm (0.055in) |
| Contact Dia. | 1.6 mm (0.063in) |
| Wire Size/AWG | 24 - 16 |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | FFA - Straight plug, cable collet |
| Plug | Straight |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | Hermaphroditic keying (half moon insert) with male pin 1 |
| Colour | Grey |
| Weight | 32 g |

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-302-clac62.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

| | |
|-----------------------------------|---|
| Technical domain | Audio Video, Energy and Industrial, Semiconductor, Test and Measurement |
| Environmental sealing (IP rating) | IP50 |
| Endurance | 5000 mating cycles |
| Temperature range | -55°C / +250°C (max. temperature valid for short periods of use.) |
| Climatic Category | 55/175/21 |
| Humidity (max) | <=95% [at 60 deg C /140 F] |
| Shielding (min) | 75 dB (10 MHz) |
| Shielding (min) | 40 dB (1 GHz) |
| Shock Resistance | 100 g [6 ms] |
| Vibration | 15 g [10 Hz - 2000 Hz] |
| Salt Spray Corrosion | >1000 hr |

Cable fixation

| | |
|------------------------------------|--|
| Cable termination protection | Standard back nut (no additional protection) |
| Fixation type | Cable collet |
| Jacket cable outside diameter [mm] | 5.30 - 6.20 mm |

Recommended By Lemo

Accessories

| | |
|----------------|---------------------------------|
| Compatible cap | BFG.2B.100.PCSG |
|----------------|---------------------------------|

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-302-clac62.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

| Cable PartNumber | Material | Colour | Cable image |
|------------------|----------|--------|---|
| 102080 | PVC | Grey | |
| 120184 | PVC | Black |  |
| 120500 | PVC | Grey |  |
| 120751 | PVC | Grey |  |
| 220750 | PVC | Grey |  |

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-302-clac62.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.