

Standard

*Image for illustrative purpose only*

Summary

[Request a quote](#)[SE series](#)[Customer Drawing](#)

Number of contacts Low Voltage	7
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.20 mm
Size	2S
Suggested matching part	ERA.2S.307.CLL PCA.2S.307.CLLC62
Series	S - Indoor Stepped Insert

Technical details

Electrical Configuration

Number of contacts Low Voltage	7
Contact Termination Low voltage	Solder
Insert configuration value	25.307 - 3 (1.3 mm) + 4 (0.9 mm) Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	1.3 mm : 12 A, 0.9 mm : 9 A
Test voltage (kV DC)	1.2
Bucket Dia.	3x1 mm, 4x0.8 mm
Contact Dia.	3x1.3 mm, 4x0.9 mm
Wire Size/AWG details	1.3 mm : 20 (AWG max), 0.9 mm : 22 (AWG max)

Form & Material

Shell style / Model id	FFA - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Weight	32.43 g

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-307-clac62.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.20 mm

Recommended By Lemo

Accessories

Compatible cap	BFG.2B.100.PCSG
----------------	---------------------------------

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-307-clac62.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.