

[Standard](#)

Image for illustrative purpose only

Summary

[Request a quote](#)[Coax triax mixed en](#)[Customer Drawing](#)

Nb of contacts Triax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.20 mm
Size	2S
Suggested matching part	ERA.2S.675.CLL
Series	S - Indoor Stepped Insert

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-675-clac62z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Triax	1
Contact Termination Triax	Solder
Insert configuration value	2S.675 - 1 Triax (75 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	6 A
Impedance	75 Ohms
VSWR	1.02 + 0.07 * f/GHz
Vtest	1200 V (AC), 1700 V (DC)
Cable type	Belden 8215,8232A,HF-2426,Triax 8 Nokia,375 029 LEDE, RGT 179

Form & Material

Shell style / Model id	FFA - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	33.96 g

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-675-clac62z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.20 mm

Recommended By Lemo

Caps

Compatible cap	BFG.2B.100.PCSG
Plastic Cap	BFG.2B.100.PCSG
Soft Cap	BFZ.2B.100.SCN

Bend Reliefs

GMA.2B.060.DG	GMA.2B.060.DA	GMA.2B.060.DB
GMA.2B.060.DJ	GMA.2B.060.DM	GMA.2B.060.DN
GMA.2B.060.DR	GMA.2B.060.DS	GMA.2B.060.DV

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffa-2s-675-clac62z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.