

Standard*Image for illustrative purpose only*

Summary

[Request a quote](#)**high voltage connector Y S E 05 LEMO**

Number of contacts High Voltage	1
Wire Size/AWG	18 - 10
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	9.80 - 10.50 mm
Size	3S
Suggested matching part	ERA.3S.405.CTL PSA.3S.405.CTLC11
Series	S - Indoor Stepped Insert

Technical details

Electrical Configuration

Number of contacts High Voltage	1
Contact Termination High voltage	Solder
Insert configuration value	35.405 - 1 High Voltage
Insulator	T: PTFE
Rated current	15 A
Test voltage (kV DC)	10.5
Air clearance	12.8 mm
Creepage distance	12.9 mm
Contact Dia.	4
Wire Size/AWG	18 - 10

Form & Material

Shell style / Model id	FFB - Straight plug, cable collet and safety locking ring
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Weight	59.75 g

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffb-3s-405-ctac11.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	9.80 - 10.50 mm

Drawings



Dimensions

	A	L	M	S2
mm.	17.8	65	50	14
in.	0.7	2.56	1.97	0.55

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffb-3s-405-ctac11.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories

Compatible cap	BFG.3B.100.PCSG
----------------	---------------------------------

Tools

Spanner wrench	DCP.91.023.TN
----------------	-------------------------------

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/ffb-3s-405-ctac11.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.