



Image for illustrative purpose only

Summary

[Request a quote](#)

[unipole multipole](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	2.30 - 2.70 mm
------------------------------------	----------------

https://www.lemo.com/int_en/ffc-00-727-cn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility	No
------------------------------------	----

Form & Material

Shell style / Model id	FFC - 00 series cable collet
------------------------	------------------------------

Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet
------------------	---

Keying	No keying
--------	-----------

Weight	0.27 g
--------	--------

Environment

Environmental sealing (IP rating)	IP50
-----------------------------------	------

Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
-------------------	---

Salt Spray Corrosion	>1000 hr
----------------------	----------

Cable fixation

Fixation type	Cable collet
---------------	--------------

Jacket cable outside diameter [mm]	2.30 - 2.70 mm
------------------------------------	----------------

https://www.lemo.com/int_en/ffc-00-727-cn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.