

Special

Image for illustrative purpose only

Summary

[Request a quote](#)[Catalog](#)

Number of contacts Low Voltage	8
Wire Size/AWG	28 - 20
Plug	Plug - Straight
Locking system	Snap-on
Jacket cable outside diameter [mm]	7.30 - 8.70 mm
Size	3S
Series	S - Indoor Stepped Insert

https://www.lemo.com/int_en/catalog/product/view/id/459186/s/fff-3s-308-clac82/category/38/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	8
Contact Termination Low voltage	Solder
R (max)	3.6 mOhm
Insert configuration value	3S.308 - 8 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	10 A
Test voltage (kV DC)	1.5
Max. Solid Conductor	0.5 mm ² (AWG 20)
Max. Stranded Conductor	0.5 mm ² (AWG 20)
Bucket Dia.	1 mm (0.039in)
Contact Dia.	1.3 mm (0.051in)
Wire Size/AWG	28 - 20

Form & Material

Shell style / Model id	FFF - Straight plug, non-latching, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Snap-on
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Weight	60.16 g

https://www.lemo.com/int_en/catalog/product/view/id/459186/s/fff-3s-308-clac82/category/38/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.30 - 8.70 mm

Drawings



Dimensions

	S2	M	L	A
mm.	13.9	48	63	18
in.	0.55	1.89	2.48	0.71

https://www.lemo.com/int_en/catalog/product/view/id/459186/s/fff-3s-308-clac82/category/38/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Tools

Spanner wrench

[DCP.91.023.TN](#)

Cables

Cable PartNumber	Material	Colour	Cable image
380500	PVC	Grey	

https://www.lemo.com/int_en/catalog/product/view/id/459186/s/fff-3s-308-clac82/category/38/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.