

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

BKT series

Wire Size/AWG	26 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Snap-on
Jacket cable outside diameter [mm]	4.10 - 4.50 mm
Size	1T
Suggested matching part	EGG.1T.308.CYM
Series	T - Small Outdoor keyed

https://www.lemo.com/int_en/solutions/originals/t-small-outdoor-keyed/ffg-1t-308-cycc45z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

R (max) - electrical contact resistance	6.1 mOhm
Rated current	5 A
Test voltage contact-contact	2 kV DC
Test voltage contact-shell	1.9 kV DC
Contact retention	22 N
Max. Conductor	0.34 mm ² (AWG 22)
Min. Conductor	0.14 mm ² (AWG 26)
Bucket Dia.	0.8 mm (0.031 in)
Contact Dia.	0.7 mm (0.028 in)
Wire Size/AWG	26 - 22
Gender	Standard

Form & Material

Shell style / Model id	FF - Straight Plug, non latching, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Snap-on
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	20.86 g

Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/t-small-outdoor-keyed/ffg-1t-308-cycc45z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.10 - 4.50 mm

Drawings



Dimensions

	A	L	M	S1	S2
mm.	12	46	35	10	9
in.	0.47	1.81	1.38	0.39	0.35

Recommended By Lemo

Contacts

Replacement contact	FGG.1B.555.ZZC
---------------------	----------------

Caps

Soft Cap	BFZ.1T.100.SCN
----------	----------------

Bend Reliefs

GMA.1B.045.DG	GMA.1B.045.DA	GMA.1B.045.DB
GMA.1B.045.DJ	GMA.1B.045.DM	GMA.1B.045.DN
GMA.1B.045.DR	GMA.1B.045.DS	GMA.1B.045.DV

Tools

Spanner	DCP.0T.110.TN
Positionner	DCE.91.071.BVC
Extraction tool	DCC.07.04B.LAG
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/originals/t-small-outdoor-keyed/ffg-1t-308-cycc45z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.08.T26.042QGZE	TPR (medical)	Grey	