



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

SE series

Number of contacts Low Voltage	16
Wire Size/AWG	30 - 22
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.30 - 8.70 mm
Size	3S
Suggested matching part	<a href="#">ERA.3S.316.CLL</a> <a href="#">PCP.3S.316.CLLC82</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/](https://www.lemo.com/int_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	16
Contact Termination Low voltage	Solder
R (max)	4.8 mOhm
Insert configuration value	3S.316 - 16 Low Voltage
Footprint IPC Class3 compatibility	No
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 A
Test voltage (kV DC)	1.5
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.9 mm (0.0354in)
Wire Size/AWG	30 - 22

## Form & Material

Shell style / Model id	FFP - Straight plug, cable collet and inner anti-rotating device
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Colour	Grey
Weight	54.38 g

[https://www.lemo.com/int\\_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/](https://www.lemo.com/int_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.30 - 8.70 mm

## Drawings



## Dimensions

	L	M	S2	A
mm.	61	46	14	17.8
in.	2.4	1.81	0.55	0.7

[https://www.lemo.com/int\\_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/](https://www.lemo.com/int_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

Compatible cap [BFG.3B.100.PCSG](#)

## Tools

Spanner wrench [DCP.91.023.TN](#)

# Cables

Cable PartNumber	Material	Colour	Cable image
CMN.16.T22.076QGZE	TPR (medical)	Grey	
216220	PVC	Black	
216240	PVC	Black	
316250	PVC	Grey	

[https://www.lemo.com/int\\_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/](https://www.lemo.com/int_en/catalog/product/view/id/454725/s/ffp-3s-316-clac82/category/38/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.