



Image for illustrative purpose only

Summary

[Request a quote](#)

[Coax triax mixed en](#)

[Customer Drawing](#)

Nb of contacts Coax	1
Size	2B
Suggested matching part	PSS.2B.250.ZTME30
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/ffs-2b-250-ztce30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Crimp
Insulator	T: PTFE
Rated current	2 A
Impedance	50 Ohms
Test voltage (kV DC)	2.26
VSWR	<1.3 DC to 6 GHz
Cable type	RG 316 /U

Form & Material

Weight	2.17 g
--------	--------

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Conductor ø max	0.58 mm
Dielectric ø max	1.65 mm
Sheath ø max	3.0 mm

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/ffs-2b-250-ztce30.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.