

[Standard](#)

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[BKT series](#)[See video assembly instructions](#)[Customer Drawing](#)

|                                    |                 |
|------------------------------------|-----------------|
| Number of contacts Low Voltage     | 7               |
| Wire Size/AWG                      | 34 - 28         |
| Gender                             | Standard        |
| Plug                               | Plug - Straight |
| Locking system                     | Push-pull       |
| Jacket cable outside diameter [mm] | 3.30 - 4.20 mm  |
| Size                               | 0B              |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fga-0b-307-clad42z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fga-0b-307-clad42z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Series

B - Indoor keyed

# Technical details

## Electrical Configuration

|                                 |                               |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage  | 7                             |
| Contact Termination Low voltage | Solder                        |
| R (max)                         | 8.7 mOhm                      |
| Insert configuration value      | 0B.307 - 7 Low Voltage        |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                   | 3 A                           |
| Test voltage contact-contact    | 1.1 kV DC                     |
| Test voltage contact-shell      | 1 kV DC                       |
| Max. Solid Conductor            | 0.09 mm <sup>2</sup> (AWG 28) |
| Max. Stranded Conductor         | 0.09 mm <sup>2</sup> (AWG 28) |
| Bucket Dia.                     | 0.45 mm (0.018in)             |
| Contact Dia.                    | 0.5 mm (0.02in)               |
| Wire Size/AWG                   | 34 - 28                       |
| Gender                          | Standard                      |

## Form & Material

|                        |                                                                                                                               |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell style / Model id | FG - Straight plug, cable collet and nut for fitting a bend relief                                                            |
| Plug                   | Straight                                                                                                                      |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull                                                                                                                     |
| Keying                 | A: 2 keys (alpha=30, plug: male contacts, receptacle: female contacts)                                                        |
| Colour                 | Grey                                                                                                                          |
| Variant                | Nut for fitting a bend relief                                                                                                 |
| Weight                 | 8.74 g                                                                                                                        |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fga-0b-307-clad42z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fga-0b-307-clad42z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |                                                                                                                                            |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50                                                                                                                                       |
| Endurance                         | 5000 mating cycles                                                                                                                         |
| Temperature range                 | -55°C / +250°C (max. temperature valid for short periods of use.)                                                                          |
| Climatic Category                 | 55/175/21                                                                                                                                  |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]                                                                                                                 |
| Shielding (min)                   | 75 dB (10 MHz)                                                                                                                             |
| Shielding (min)                   | 40 dB (1 GHz)                                                                                                                              |
| Shock Resistance                  | 100 g [ 6 ms]                                                                                                                              |
| Vibration                         | 15 g [10 Hz - 2000 Hz]                                                                                                                     |
| Salt Spray Corrosion              | >1000 hr                                                                                                                                   |

## Cable fixation

|                                    |                       |
|------------------------------------|-----------------------|
| Cable termination protection       | For cable bend relief |
| Fixation type                      | Cable collet          |
| Jacket cable outside diameter [mm] | 3.30 - 4.20 mm        |

# Recommended By Lemo

## Caps

|          |                                |
|----------|--------------------------------|
| Soft Cap | <a href="#">BFZ.0B.100.SCN</a> |
|----------|--------------------------------|

## Bend Reliefs

|                               |                               |                               |
|-------------------------------|-------------------------------|-------------------------------|
| <a href="#">GMA.0B.035.DG</a> | <a href="#">GMA.0B.035.DA</a> | <a href="#">GMA.0B.035.DB</a> |
| <a href="#">GMA.0B.035.DJ</a> | <a href="#">GMA.0B.035.DM</a> | <a href="#">GMA.0B.035.DN</a> |
| <a href="#">GMA.0B.035.DR</a> | <a href="#">GMA.0B.035.DS</a> | <a href="#">GMA.0B.035.DV</a> |

## Tools

|                |                                  |
|----------------|----------------------------------|
| Spanner        | <a href="#">DCP.91.001.TN</a>    |
| Spanner wrench | <a href="#">DCD.0B.ZZZ.PA070</a> |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fga-0b-307-clad42z.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fga-0b-307-clad42z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Cables

| Cable PartNumber | Material | Colour | Cable image                                                                         |
|------------------|----------|--------|-------------------------------------------------------------------------------------|
| 7050             | PVC      | Black  |  |