

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[See video assembly instructions](#)

[Customer Drawing](#)

Number of contacts Low Voltage	4
Wire Size/AWG	14 - 10
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	15.10 - 16.00 mm
Size	4B
Suggested matching part	EGB.4B.304.CYM

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-4b-304-cycd16.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Crimp
R (max) - electrical contact resistance	3.1 mOhm
Insert configuration value	4B.304 - 4 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	30 A
Test voltage contact-contact	2.6 kV DC
Test voltage contact-shell	1.7 kV DC
Contact retention	75 N
Max. Conductor	4 mm ² (AWG 10)
Min. Conductor	2.5 mm ² (AWG 14)
Bucket Dia.	3.2 mm (0.126 in)
Contact Dia.	3 mm (0.118 in)
Wire Size/AWG	14 - 10
Gender	Standard

Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	B: 2 keys (alpha=45, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	118.04 g

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-4b-304-cycd16.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	15.10 - 16.00 mm

Recommended By Lemo

Contacts

Replacement contact	FGG.4B.580.ZZC
---------------------	--------------------------------

Caps

Compatible cap	BFA.4B.100.NAS
----------------	--------------------------------

Tools

Positionner	DCE.91.304.BVCM
Extraction tool	DCC.30.35B.LAG
Crimp tool	DPC.91.102.V

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgb-4b-304-cycd16.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.