

Standard*Image for illustrative purpose only*

Summary

[Request a quote](#)[unipole multipole](#)[Customer Drawing](#)

Number of contacts Low Voltage	4
Wire Size/AWG	32 - 28
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.80 - 3.50 mm
Size	00
Suggested matching part	EGG.00.304.CYM PHG.00.304.CYMD35
Series	B - Indoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Crimp
R (max)	8.7 mOhm
Insert configuration value	0.304 - 4 Low Voltage
Footprint IPC Class3 compatibility	No
Rated current	2.5 A
Vtest (contact-contact)	1.5 kV (DC)
Vtest (contact-shell)	1.5 kV (DC)
Max. Conductor	0.035 mm ² (AWG 32)
Min. Conductor	0.09 mm ² (AWG 28)
Bucket Dia.	0.45 mm (0.02in)
Contact Dia.	0.5 mm (0.02in)
Wire Size/AWG	32 - 28
Gender	Standard

Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	4.5 g

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-00-304-cycd35.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Environmental sealing (IP rating)	IP50
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	2.80 - 3.50 mm

Recommended By Lemo

Accessories

Replacement contact	FGG.00.554.ZZC
Compatible cap	BFG.00.100.PCSG

Tools

Positionner	DCE.91.050.0VC
Extraction tool	DCC.05.02B.LAG
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-00-304-cycd35.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.04.T28.031PGCE	PVC	GREY	
CMN.04.T28.031PGZE		grey	
CMN.04.T28.031PNCE	PVC	Black	
CMN.04.T28.031PNZE			
CMN.04.T28.031QGC	TPR	Grey	
4041	PVC	Grey	
4050	PVC	Black	

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-00-304-cycd35.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.