

Standard



Image for illustrative purpose only

## Summary

[Request a quote](#)

[BKT series](#)

[See video assembly instructions](#)

[Customer Drawing](#)

|                                    |                 |
|------------------------------------|-----------------|
| Number of contacts Low Voltage     | 7               |
| Wire Size/AWG                      | 34 - 28         |
| Gender                             | Standard        |
| Plug                               | Plug - Straight |
| Locking system                     | Push-pull       |
| Jacket cable outside diameter [mm] | 5.30 - 5.60 mm  |
| Size                               | 0B              |

Series

B - Indoor keyed

# Technical details

## Electrical Configuration

|                                    |                               |
|------------------------------------|-------------------------------|
| Number of contacts Low Voltage     | 7                             |
| Contact Termination Low voltage    | Solder                        |
| R (max)                            | 8.7 mOhm                      |
| Insert configuration value         | 0B.307 - 7 Low Voltage        |
| Footprint IPC Class3 compatibility | No                            |
| Insulator                          | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                      | 3 A                           |
| Vtest (contact-contact)            | 1.1 kV (DC)                   |
| Vtest (contact-shell)              | 1 kV (DC)                     |
| Max. Solid Conductor               | 0.09 mm <sup>2</sup> (AWG 28) |
| Max. Stranded Conductor            | 0.09 mm <sup>2</sup> (AWG 28) |
| Bucket Dia.                        | 0.45 mm (0.018in)             |
| Contact Dia.                       | 0.5 mm (0.02in)               |
| Wire Size/AWG                      | 34 - 28                       |
| Gender                             | Standard                      |

## Form & Material

|                        |                                                                                                                               |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell style / Model id | FG - Straight plug, cable collet                                                                                              |
| Plug                   | Straight                                                                                                                      |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull                                                                                                                     |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)                                                          |
| Colour                 | Grey                                                                                                                          |
| Weight                 | 8.31 g                                                                                                                        |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-0b-307-clad56.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-0b-307-clad56.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |                                                                                                                                            |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50                                                                                                                                       |
| Endurance                         | 5000 mating cycles                                                                                                                         |
| Temperature range                 | -55°C / +250°C (max. temperature valid for short periods of use.)                                                                          |
| Climatic Category                 | 55/175/21                                                                                                                                  |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]                                                                                                                 |
| Shielding (min)                   | 75 dB (10 MHz)                                                                                                                             |
| Shielding (min)                   | 40 dB (1 GHz)                                                                                                                              |
| Shock Resistance                  | 100 g [ 6 ms]                                                                                                                              |
| Vibration                         | 15 g [10 Hz - 2000 Hz]                                                                                                                     |
| Salt Spray Corrosion              | >1000 hr                                                                                                                                   |

## Cable fixation

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Cable termination protection       | Standard back nut (no additional protection) |
| Fixation type                      | Cable collet                                 |
| Jacket cable outside diameter [mm] | 5.30 - 5.60 mm                               |

# Recommended By Lemo

## Accessories

|                |                                 |
|----------------|---------------------------------|
| Compatible cap | <a href="#">BFG.0B.100.PCZG</a> |
|----------------|---------------------------------|

## Tools

|                |                                  |
|----------------|----------------------------------|
| Spanner        | <a href="#">DCP.91.001.TN</a>    |
| Spanner wrench | <a href="#">DCD.0B.ZZZ.PA070</a> |

# CAD

## Documents

|       |                          |
|-------|--------------------------|
| Eplan | <a href="#">Download</a> |
|-------|--------------------------|

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-0b-307-clad56.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-0b-307-clad56.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.