

Special



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

|                                    |                                |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage     | 5                              |
| Wire Size/AWG                      | 30 - 22                        |
| Gender                             | Standard                       |
| Plug                               | Plug - Straight                |
| Locking system                     | Push-pull                      |
| Jacket cable outside diameter [mm] | 4.60 - 5.00 mm                 |
| Size                               | 0T                             |
| Suggested matching part            | <a href="#">EGG.0T.305.KYM</a> |
| Series                             | T - Small Outdoor keyed        |

[https://www.lemo.com/int\\_en/solutions/originals/t-small-outdoor-keyed/fgg-0t-305-klac50z.html](https://www.lemo.com/int_en/solutions/originals/t-small-outdoor-keyed/fgg-0t-305-klac50z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Number of contacts Low Voltage          | 5                             |
| Contact Termination Low voltage         | Solder                        |
| R (max) - electrical contact resistance | 6.1 mOhm                      |
| Insert configuration value              | T.305 - 5 Low Voltage         |
| Insulator                               | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                           | 6.5 A                         |
| Test voltage contact-contact            | 1.4 kV DC                     |
| Test voltage contact-shell              | 1 kV DC                       |
| Max. Conductor                          | 0.34 mm <sup>2</sup> (AWG 22) |
| Max. Stranded Conductor                 | 0.34 mm <sup>2</sup> (AWG 22) |
| Bucket Dia.                             | 0.8 mm (0.031 in)             |
| Contact Dia.                            | 0.7 mm (0.028 in)             |
| Wire Size/AWG                           | 30 - 22                       |
| Gender                                  | Standard                      |

## Form & Material

|                        |                                                                                                               |
|------------------------|---------------------------------------------------------------------------------------------------------------|
| Shell style / Model id | FG - Straight plug, cable collet and nut for fitting a bend relief                                            |
| Plug                   | Straight                                                                                                      |
| Housing material       | Brass (black chrome) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull                                                                                                     |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)                                          |
| Colour                 | Black                                                                                                         |
| Variant                | Nut for fitting a bend relief                                                                                 |
| Weight                 | 8.38 g                                                                                                        |

[https://www.lemo.com/int\\_en/solutions/originals/t-small-outdoor-keyed/fgg-0t-305-klac50z.html](https://www.lemo.com/int_en/solutions/originals/t-small-outdoor-keyed/fgg-0t-305-klac50z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |                                                                   |
|-----------------------------------|-------------------------------------------------------------------|
| Technical domain                  | Energy and Industrial, Test and Measurement                       |
| Environmental sealing (IP rating) | IP68                                                              |
| Endurance                         | >3000 mating cycles                                               |
| Temperature range                 | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatic Category                 | 50/175/21                                                         |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]                                        |
| Shock Resistance                  | 100 g [ 6 ms]                                                     |
| Vibration                         | 15 g [10 Hz - 2000 Hz]                                            |
| Salt Spray Corrosion              | >1000 hr                                                          |

## Cable fixation

|                                    |                       |
|------------------------------------|-----------------------|
| Cable termination protection       | For cable bend relief |
| Fixation type                      | Cable collet          |
| Jacket cable outside diameter [mm] | 4.60 - 5.00 mm        |

# Recommended By Lemo

## Caps

|                |                                |
|----------------|--------------------------------|
| Compatible cap | <a href="#">BFG.0T.100.KAS</a> |
| Soft Cap       | <a href="#">BFZ.0T.100.SCN</a> |

## Bend Reliefs

|                               |                               |                               |
|-------------------------------|-------------------------------|-------------------------------|
| <a href="#">GMA.0B.045.DG</a> | <a href="#">GMA.0B.045.DA</a> | <a href="#">GMA.0B.045.DB</a> |
| <a href="#">GMA.0B.045.DJ</a> | <a href="#">GMA.0B.045.DM</a> | <a href="#">GMA.0B.045.DN</a> |
| <a href="#">GMA.0B.045.DR</a> | <a href="#">GMA.0B.045.DS</a> | <a href="#">GMA.0B.045.DV</a> |

## Tools

|         |                               |
|---------|-------------------------------|
| Spanner | <a href="#">DCP.0T.110.TN</a> |
|---------|-------------------------------|

[https://www.lemo.com/int\\_en/solutions/originals/t-small-outdoor-keyed/fgg-0t-305-klac50z.html](https://www.lemo.com/int_en/solutions/originals/t-small-outdoor-keyed/fgg-0t-305-klac50z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.