

Standard

*Image for illustrative purpose only*

Summary

[Request a quote](#)[BKT series](#)[Customer Drawing](#)

Number of contacts Low Voltage	14
Wire Size/AWG	32 - 28
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.10 - 5.50 mm
Size	1K
Suggested matching part	EGG.1K.314.CLL
Series	K - Outdoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	14
Contact Termination Low voltage	Crimp
R (max)	8.7 mOhm
Insert configuration value	1K.314 - 14 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	2 A
Vtest (contact-contact)	1.9 kV (DC)
Vtest (contact-shell)	2.1 kV (DC)
Contact retention	12 N
Max. Conductor	0.09 mm ² (AWG 28)
Min. Conductor	0.035 mm ² (AWG 32)
Bucket Dia.	0.45 mm (0.018in)
Contact Dia.	0.5 mm (0.02in)
Wire Size/AWG	32 - 28
Gender	Standard

Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	23.55 g

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-1k-314-cycc55.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.10 - 5.50 mm

Recommended By Lemo

Accessories

Replacement contact	FGG.1B.554.ZZC
Compatible cap	BFG.1K.100.NAS

Tools

Positionner	DCE.91.051.BVC
Extraction tool	DCC.05.02B.LAG
Crimp tool	DPC.91.701.V
Spanner wrench	DCD.1E.ZZZ.PA090

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-1k-314-cycc55.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

CAD

Documents

Eplan

[Download](#)

https://www.lemo.com/int_en/solutions/originals/k-outdoor-keyed/fgg-1k-314-cycc55.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.