



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	6.30 - 7.20 mm
------------------------------------	----------------

Size	2B
------	----

Series	B - Indoor keyed
--------	------------------

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-772-dn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility

No

Form & Material

Shell style / Model id

FG - B series cable collet

Housing material

Brass (nickel plated [SAE AMS QQ N 290]) collet

Keying

No keying

Weight

3.9 g

Environment

Technical domain

Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV

Environmental sealing (IP rating)

IP50

Temperature range

-55°C / +250°C (max. temperature valid for short periods of use.)

Salt Spray Corrosion

>1000 hr

Cable fixation

Fixation type

Cable collet

Jacket cable outside diameter [mm]

6.30 - 7.20 mm

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-2b-772-dn.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.