



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[P series catalog](#)

Number of contacts Low Voltage	15
Wire Size/AWG	30 - 22
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.60 - 8.50 mm
Size	3P
Suggested matching part	<a href="#">EGG.3P.314.NLWN</a> <a href="#">PHG.3P.314.NLWD85N</a>
Series	REDEL P - Push-Pull

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	15
Contact Termination Low voltage	Solder
Insert configuration value	3P.314 - 14 Low Voltage + 1 Ground contact
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 A
Test voltage contact-contact	1.7 kV DC
Air clearance	0.9 mm
Creepage distance	0.9 mm
Contact Dia.	0.9
Wire Size/AWG	30 - 22

## Form & Material

Shell style / Model id	FG - Straight plug with key and cable seal
Plug	Straight
Housing material	PSU (Polysulfone), black
Locking system	Push-pull
Keying	User configurable, 1 of 11 key positions. Plug: male contacts, Receptacle: female contacts
Colour	Black
Variant	Black front ring
Weight	21.21 g

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP61
Endurance	>3000 mating cycles
Temperature range	-50°C / +150°C
F ret (max)	200 N
F ret (min)	100 N
Steam sterilization	Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us.



[https://www.lemo.com/int\\_en/solutions/redele/redele-p-push-pull/fgg-3p-314-nlwd85n.html](https://www.lemo.com/int_en/solutions/redele/redele-p-push-pull/fgg-3p-314-nlwd85n.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.60 - 8.50 mm

## Drawings



## Dimensions

	A	L
mm.	21.2	63
in.	0.83	2.48

## Recommended By Lemo

### Accessories

Replacement contact	EGG.3P.661.ZZY
---------------------	----------------