

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[P series catalog](#)

Number of contacts Low Voltage

1

Size

3P

Series

REDEL P - Push-Pull

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.9


## Form & Material

Shell style / Model id	FG - Male earthing contact for REDEL 3P series
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.42 g

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Endurance	1000 mating cycles
Temperature range	-50°C / +150°C

## Drawings



No keying

## Dimensions

	A	C
mm.	0.9	2.0
in.	0.04	0.08

# Recommended By Lemo

## Tools

---

Crimp tool

DPC.91.701.V

[https://www.lemo.com/int\\_en/solutions/redeI/redeI-p-push-pull/fgg-3p-561-zzy.html](https://www.lemo.com/int_en/solutions/redeI/redeI-p-push-pull/fgg-3p-561-zzy.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.