

Special

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[BKT series](#)[Customer Drawing](#)

|                                    |                                |
|------------------------------------|--------------------------------|
| Number of contacts Low Voltage     | 4                              |
| Gender                             | Standard                       |
| Plug                               | Plug - Straight                |
| Locking system                     | Push-pull                      |
| Jacket cable outside diameter [mm] | 2.70 - 3.00 mm                 |
| Size                               | TT                             |
| Suggested matching part            | <a href="#">EGG.TT.304.KLL</a> |
| Series                             | T - Small Outdoor keyed        |

# Technical details

## Electrical Configuration

|                                 |                               |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage  | 4                             |
| Contact Termination Low voltage | Solder                        |
| R (max)                         | 8.7 mOhm                      |
| Insert configuration value      | T.304 - 4 Low Voltage         |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                   | 2.5 A                         |
| Vtest (contact-contact)         | 1.1 kV (DC)                   |
| Vtest (contact-shell)           | 0.9 kV (DC)                   |
| Max. Solid Conductor            | 0.09 mm <sup>2</sup> (AWG 28) |
| Max. Stranded Conductor         | 0.09 mm <sup>2</sup> (AWG 28) |
| Bucket Dia.                     | 0.45 mm (0.018in)             |
| Contact Dia.                    | 0.5 mm (0.02in)               |
| Gender                          | Standard                      |

## Form & Material

|                        |   |
|------------------------|---|
| Shell style / Model id | FG - Straight plug, cable collet and nut for fitting a bend relief  |
| Plug                   | Straight  |
| Housing material       | Brass (black chrome) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull   |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)  |
| Colour                 | Black   |
| Variant                | Nut for fitting a bend relief   |
| Weight                 | 7.85 g  |

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-tt-304-klac31z.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-tt-304-klac31z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |   |
|-----------------------------------|---|
| Technical domain                  | Energy and Industrial, Test and Measurement                       |
| Environmental sealing (IP rating) | IP68  |
| Endurance                         | >3000 mating cycles   |
| Temperature range                 | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatic Category                 | 50/175/21   |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]  |
| Shock Resistance                  | 100 g [ 6 ms]   |
| Vibration                         | 15 g [10 Hz - 2000 Hz]  |
| Salt Spray Corrosion              | >1000 hr  |

## Cable fixation

|                                    |                       |
|------------------------------------|-----------------------|
| Cable termination protection       | For cable bend relief |
| Fixation type                      | Cable collet          |
| Jacket cable outside diameter [mm] | 2.70 - 3.00 mm        |

## Recommended By Lemo

### Accessories

|                |                                |
|----------------|--------------------------------|
| Compatible cap | <a href="#">BFG.TT.100.KAS</a> |
|----------------|--------------------------------|

## CAD

### Documents

|       |                          |
|-------|--------------------------|
| Eplan | <a href="#">Download</a> |
|-------|--------------------------|

## Cables

| Cable PartNumber | Material | Colour | Cable image   |
|------------------|----------|--------|---|
| 4041             | PVC      | Grey   |  |
| 4050             | PVC      | Black  |  |

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/fgg-tt-304-klac31z.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/fgg-tt-304-klac31z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.