

Special*Image for illustrative purpose only*

Summary

[Request a quote](#)[M series](#)[Customer Drawing](#)

High Power	3
Wire Size/AWG	8 - 8
Gender	Reverse Gender
Plug	Plug - Straight
Locking system	Ratchet
Size	5M
Series	M - Rugged Ratchet coupling

Technical details

Electrical Configuration

High Power	3
Contact Termination High Power	Crimp
Insert configuration value	5M.H34 - 3 High Power (4 mm)
Insulator	L: PEEK
Rated current	52 A
Test voltage contact-contact	9 kV rms
Test voltage contact-shell	4.7 kV rms
Wire Size/AWG	8 - 8
Gender	Reverse Gender

Form & Material

Shell style / Model id	FG - Straight plug with arctic grip and mold stop
Plug	Straight
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	X: 5 keys (alpha=100, beta=125, gamma=40, delta=20, plug: female contacts, receptacle: male contacts)
Colour	Grey
Weight	27.64 g

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgx-5m-h34-xlmt.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lightning strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Cable fixation

Cable termination protection	For overmolding
Fixation type	Mold stop (overmolding)

Recommended By Lemo

Accessories

Compatible cap	BGF.5M.100.XAV
----------------	--------------------------------

Tools

Extraction tool	DCC.91.43H.PL
-----------------	-------------------------------

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/fgx-5m-h34-xlmt.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.