

Standard

*Image for illustrative purpose only*

Summary

[Request a quote](#)[Coax triax mixed en](#)[Customer Drawing](#)

Nb of contacts Coax	1
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 6.00 mm
Size	1S
Suggested matching part	ERA.1S.275.CTME61 PGZ.1S.275.CTME61Z
Series	S - Indoor Stepped Insert

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Crimp
Insert configuration value	15.275 - 1 Coax (75 Ohm)
Footprint IPC Class3 compatibility	No
Insulator	T: PTFE
Rated current	3 A
Impedance	75 Ohms
VSWR	Compliant to SMPTE 2082-1 norm. See catalogue for more information.
Vtest	1200 V (AC)
Cable type	DRAKA ULTRA PRO 50 HD, BELDEN 4855R
Bucket Dia.	0.75 mm (0.03in)
Contact Dia.	0.6 mm (0.02in)

Form & Material

Shell style / Model id	FGZ - Straight plug - design chocolate block, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Weight	22.3 g

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fgz-1s-275-ctce61z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	1000 mating cycles
Temperature range	-55°C / +260°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Crimp
Jacket cable outside diameter [mm]	4.00 - 6.00 mm

Recommended By Lemo

Tools

Spanner	DCP.91.001.TN
Crimp tool	DPE.99.127.0K

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fgz-1s-275-ctce61z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.