

Special



Image for illustrative purpose only

## Summary

[Request a quote](#)

BKT series

Number of contacts Low Voltage	26
Wire Size/AWG	34 - 28
Gender	Standard
Plug	Plug - Elbow
Locking system	Push-pull
Jacket cable outside diameter [mm]	8.30 - 9.20 mm
Size	2B
Suggested matching part	<a href="#">EGB.2B.326.CLL</a>
Alternative part	<a href="#">FPB.2B.326.CLAD92</a>
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/catalog/product/view/id/491868/s/fhb-2b-326-clad92/category/23/](https://www.lemo.com/int_en/catalog/product/view/id/491868/s/fhb-2b-326-clad92/category/23/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	26
Contact Termination Low voltage	Solder
R (max)	8.7 mOhm
Insert configuration value	2B.326 - 26 Low Voltage
Footprint IPC Class3 compatibility	No
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	1.5 A
Vtest (contact-contact)	1 kV (DC)
Vtest (contact-shell)	1.9 kV (DC)
Max. Solid Conductor	0.09 mm <sup>2</sup> (AWG 28)
Max. Stranded Conductor	0.09 mm <sup>2</sup> (AWG 28)
Bucket Dia.	0.45 mm (0.018in)
Contact Dia.	0.5 mm (0.02in)
Wire Size/AWG	34 - 28
Gender	Standard

## Form & Material

Shell style / Model id	FH - Elbow plug, cable collet
Plug	Elbow
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	2 keys (alpha=45, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	40.17 g

[https://www.lemo.com/int\\_en/catalog/product/view/id/491868/s/fhb-2b-326-clad92/category/23/](https://www.lemo.com/int_en/catalog/product/view/id/491868/s/fhb-2b-326-clad92/category/23/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.30 - 9.20 mm

## Drawings



## Dimensions

	A	D	H	L	M	S1	S2	S3
mm.	16.5	9	34	41.5	29.5	14	12	13
in.	0.65	0.35	1.34	1.63	1.16	0.55	0.47	0.51

[https://www.lemo.com/int\\_en/catalog/product/view/id/491868/s/fhb-2b-326-clad92/category/23/](https://www.lemo.com/int_en/catalog/product/view/id/491868/s/fhb-2b-326-clad92/category/23/)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Documents

---

Eplan

[Download](#)