



Image for illustrative purpose only

Summary

[Request a quote](#)

[W series en](#)

[Customer Drawing](#)

Number of contacts Low Voltage	10
Wire Size/AWG	30 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Threaded
Jacket cable outside diameter [mm]	8.10 - 8.50 mm
Size	2W
Suggested matching part	HVA.2W.310.CLLPV PVA.2W.310.CLLC85
Series	W - Underwater

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fva-2w-310-clac85.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Solder
R (max) - electrical contact resistance	4.8 mOhm
Insert configuration value	2W.310 - 10 Low Voltage
Rated current	8 A
Test voltage contact-contact	1450 V (AC) 2100 V (DC)
Test voltage contact-shell	1300 V (AC) 1800 V (DC)
Max. Solid Conductor	0.34 mm ² (AWG 22)
Max. Stranded Conductor	0.34 mm ² (AWG 22)
Bucket Dia.	0.8 mm (0.031 in)
Contact Dia.	0.9 mm (0.035 in)
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	FV - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	A: 2 keys (alpha=30, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	51.24 g

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fva-2w-310-clac85.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.10 - 8.50 mm

Recommended By Lemo

Caps

Compatible cap	BFA.2W.100.NAZ
----------------	--------------------------------

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fva-2w-310-clac85.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.