



Image for illustrative purpose only

Summary

[Request a quote](#)

[W series en](#)

Number of contacts Low Voltage	4
Nb of contacts Fiber optic	2
Gender	Standard
Plug	Plug - Straight
Locking system	Threaded
Size	3W
Suggested matching part	EVG.3W.93B.CLL
Series	W - Underwater

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-3w-93b-clat91z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	4
Contact Termination Low voltage	Solder
Nb of contacts Fiber optic	2
Gender	Standard

Form & Material

Shell style / Model id	FV_Z - Straight plug, cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	G: 1 key (alpha=0, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	96.2 g

Environment

Technical domain	Specialties and Other
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	30 bars
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/supreme/w-underwater/fvg-3w-93b-clat91z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	T type cable adapter

Drawings



Dimensions

	A	B	L	M	N	S1	S3
mm.	27.8	17	60.5	46.9	16.5	26	15
in.	1.09	0.67	2.38	1.85	0.65	1.02	0.59

Recommended By Lemo

Caps

Compatible cap	BFG.3W.100.NAZ
----------------	--------------------------------