

Standard*Image for illustrative purpose only*

Summary

[Request a quote](#)[Catalog](#)[Customer Drawing](#)

| | |
|------|----|
| Size | 00 |
|------|----|

| | |
|--------|----------------|
| Series | 00 - NIM-CAMAC |
|--------|----------------|

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/gca-00-255-lt.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

| | |
|------------------------|-----------------------|
| Shell style / Model id | GCA - Earthing washer |
| Housing material | Brass (CuSnZn plated) |
| Keying | No keying |
| Weight | 0.19 g |

Environment

| | |
|-----------------------------------|--------------|
| Environmental sealing (IP rating) | No IP rating |
|-----------------------------------|--------------|

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/gca-00-255-1t.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.