

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Size	0B
Series	B - Indoor keyed

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility	No
------------------------------------	----

Form & Material

Shell style / Model id	GMA - Bend relief Black
Housing material	Silicone elastomer VMQ
Keying	No keying
Colour	Black
Weight	0.42 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-60°C / +200°C (max. temperature valid for short periods of use.)
Temperature range in water steam	+140°C

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-0b-018-rn.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.