

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	2.50 - 2.90 mm
Size	0B
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-0b-025-rs.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Shell style / Model id	GMA - Bend relief Orange
------------------------	--------------------------

Housing material	Silicone elastomer VMQ
------------------	------------------------

Keying	No keying
--------	-----------

Colour	Orange
--------	--------

Weight	0.44 g
--------	--------

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
------------------	--

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Temperature range	-60°C / +200°C (max. temperature valid for short periods of use.)
-------------------	---

Temperature range in water steam	+140°C
----------------------------------	--------

Cable fixation

Jacket cable outside diameter [mm]	2.50 - 2.90 mm
------------------------------------	----------------

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-0b-025-rs.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.