

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

|                                    |                  |
|------------------------------------|------------------|
| Jacket cable outside diameter [mm] | 3.50 - 3.90 mm   |
| Size                               | 0B               |
| Series                             | B - Indoor keyed |

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-0b-035-rj.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-0b-035-rj.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

|                        |                          |
|------------------------|--------------------------|
| Shell style / Model id | GMA - Bend relief Yellow |
| Housing material       | Silicone elastomer VMQ   |
| Keying                 | No keying                |
| Colour                 | Yellow                   |
| Variant                | Yellow                   |
| Weight                 | 0.43 g                   |

## Environment

|                                   |                                                                                                                                            |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | No IP rating                                                                                                                               |
| Temperature range                 | -60°C / +200°C (max. temperature valid for short periods of use.)                                                                          |
| Temperature range in water steam  | +140°C                                                                                                                                     |

## Cable fixation

|                                    |                |
|------------------------------------|----------------|
| Jacket cable outside diameter [mm] | 3.50 - 3.90 mm |
|------------------------------------|----------------|

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-0b-035-rj.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-0b-035-rj.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.