

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	4.00 - 4.40 mm
Size	1B
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-040-rs.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Form & Material

Shell style / Model id GMA - Bend relief Orange

Housing material Silicone elastomer VMQ

Keying No keying

Colour Orange

Weight 1.04 g

Environment

Technical domain Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV

Environmental sealing (IP rating) No IP rating

Temperature range -60°C / +200°C (max. temperature valid for short periods of use.)

Temperature range in water steam +140°C

Cable fixation

Jacket cable outside diameter [mm] 4.00 - 4.40 mm

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-040-rs.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.