

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

---

[BKT series](#)

---

[Customer Drawing](#)

Jacket cable outside diameter [mm]	6.30 - 7.00 mm
Size	1B
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-1b-063-rs.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-063-rs.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

---

Shell style / Model id	GMA - Bend relief Orange
Housing material	Silicone elastomer VMQ
Keying	No keying
Colour	Orange
Weight	1.35 g

---

## Environment

---

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Temperature range	-60°C / +200°C (max. temperature valid for short periods of use.)
Temperature range in water steam	+140°C

---

## Cable fixation

---

Jacket cable outside diameter [mm]	6.30 - 7.00 mm
------------------------------------	----------------

---

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/gma-1b-063-rs.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-1b-063-rs.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.