

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[BKT series](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	10.00 - 10.90 mm
Size	4B
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-4b-010-da.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility	No
------------------------------------	----

Form & Material

Shell style / Model id	GMA - Bend relief Blue
------------------------	------------------------

Housing material	Thermoplastic polyurethane
------------------	----------------------------

Keying	No keying
--------	-----------

Colour	Blue
--------	------

Weight	5.5 g
--------	-------

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
------------------	--

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Temperature range	-40°C / +80°C
-------------------	---------------

Cable fixation

Jacket cable outside diameter [mm]	10.00 - 10.90 mm
------------------------------------	------------------

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/gma-4b-010-da.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.