

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[unipole multipole](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	2.80 - 3.10 mm
Size	00

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility	No
------------------------------------	----

Form & Material

Shell style / Model id	GMB - Bend relief Black
Housing material	Thermoplastic polyurethane
Keying	No keying
Colour	Black
Weight	0.41 g

Environment

Environmental sealing (IP rating)	No IP rating
-----------------------------------	--------------

Cable fixation

Jacket cable outside diameter [mm]	2.80 - 3.10 mm
------------------------------------	----------------

https://www.lemo.com/int_en/gmb-00-028-dn.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.