



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[P series catalog](#)

Number of contacts Low Voltage	6
Wire Size/AWG	26 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 6.50 mm
Size	1P
Suggested matching part	<a href="#">PLG.M0.6NY.YN</a> <a href="#">PRG.M0.6NY.YC65N</a>
Series	REDEL P - Push-Pull

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	6
Contact Termination Low voltage	Crimp
Insert configuration value	1P.M06_Y - 4 (0.5 mm) + 2 (1.3 mm) Low Voltage
Rated current	6 A
Test voltage contact-contact	1.48 (kV DC)
Air clearance	0.85 mm
Creepage distance	0.85 mm
Wire Size/AWG	26 - 22
Gender	Standard

## Form & Material

Shell style / Model id	PA - Straight plug with cable collet
Plug	Straight
Housing material	PSU (Polysulfone), black
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Black
Variant	Black collet nut
Weight	5.22 g

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +150°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us.

[https://www.lemo.com/int\\_en/solutions/redele/redele-p-push-pull/pag-m0-6ny-yc65n.html](https://www.lemo.com/int_en/solutions/redele/redele-p-push-pull/pag-m0-6ny-yc65n.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.30 - 6.50 mm

## Drawings

