

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

BKT series

Number of contacts Low Voltage	20
Wire Size/AWG	24 - 20
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Panel Drill Hole	M25
Jacket cable outside diameter [mm]	8.20 - 9.20 mm
Size	4B
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pfg-4b-320-cymm92z.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	20
Contact Termination Low voltage	Crimp
R (max) - electrical contact resistance	4.8 mOhm
Insert configuration value	4B.320 - 20 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	8 A
Test voltage contact-contact	2.7 kV DC
Test voltage contact-shell	2.6 kV DC
Contact retention	30 N
Max. Conductor	0.5 mm ² (AWG 20)
Min. Conductor	0.25 mm ² (AWG 24)
Bucket Dia.	1.1 mm (0.043 in)
Contact Dia.	0.9 mm (0.035 in)
Wire Size/AWG	24 - 20
Gender	Standard

Form & Material

Shell style / Model id	PF - Fixed receptacle, with two nuts, cable collet (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Nut for fitting a bend relief
Weight	167.2 g
Panel Drill Hole	M25

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pfg-4b-320-cymm92z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr
Cable fixation	
Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	8.20 - 9.20 mm

Drawings

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pfg-4b-320-cymm92z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	A	B	e	E	L	M	S1	S2	S3
mm.	30	32	M25x1.0	11	69	4.5	23.5	20	30
in.	1.18	1.26		0.43	2.72	0.18	0.93	0.79	1.18

Recommended By Lemo

Contacts

Replacement contact [EGG.4B.660.ZZM](#)

Caps

Compatible cap [BRE.4S.200.NAS](#)

Cap 2 [BRE.4S.200.NAV](#)

Bend Reliefs

[GMA.2B.080.DG](#) [GMA.2B.080.DA](#) [GMA.2B.080.DB](#)

[GMA.2B.080.DJ](#) [GMA.2B.080.DM](#) [GMA.2B.080.DN](#)

[GMA.2B.080.DR](#) [GMA.2B.080.DS](#) [GMA.2B.080.DV](#)

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pfg-4b-320-cymm92z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Tools

Spanner 2	DCM.65.270.AZ
Positionner	DCE.91.094.BVM
Extraction tool	DCC.09.05B.LAG
Crimp tool	DPC.91.701.V
Spanner wrench	DCM.65.270.AZ

Cables

Cable PartNumber	Material	Colour	Cable image
420250	PVC	Grey	

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/pfg-4b-320-cymm92z.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.